



SPECIFICATION SHEET

A19 General Purpose Incandescent Lamp, 2-Pack

Item Number **0337229**

Specifications

Energy Used (Watts).....	60
Domestic Code	60A/F/VR 2PK
Volts	120
Brightness (Lumens)	625
Average Rated Hours	1000
Life (in years)*.....	0.9
Dimmable.....	Yes
Filament Type.....	C9-3A
Estimated Yearly Energy Cost**.....	\$7.23
Package Type.....	Box
Country of Origin.....	China



Physical Characteristics

Finish.....	Frost
Base.....	Medium (E26)
MOL.....	4.13"

Vibration Resistant lamps are designed for vibration service only.

*Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.

Used under license by Westinghouse Lighting. All Rights Reserved.