



Powering Business Worldwide

pe.eaton.com

Type GHQ Thermal-Magnetic Circuit Breakers

GHQ1015

UPC:782114985106

Dimensions:

- **Height:** 4 IN
- **Length:** 2.63 IN
- **Width:** 3 IN

Notes:Includes 4A33462H01 load clip.

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 15A
- **Interrupt Rating:** 14 kAIC
- **Voltage Rating:** 277V
- **Circuit Breaker Type:** GHP
- **Trip Type:** Non-Interchangeable
- **Frame Size:** GDB-Frame

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [MOEM MCCB Product Selection Guide](#)
- [G-frame Molded Case Circuit Breaker Drawing](#)
- [Series C G-Frame Time Current Curves](#)
- [Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve](#)

Certifications: No Data

Product compliance: No Data

