

Project Name

Location

Prepared By



SATCO S3474

150W DOUBLE ENV. - CLEAR

Notes

General

Status	Active
Watts	150
Volts	120V
Shape	T10
Base	Medium
ANSI Base	E26
CCT (Kelvin)	2900
Temperature	Warm White
CRI	100
Lumens	2600
Beam Spread	360
Dimmable	Yes Dimmable
Hours Rated	2000
Lamp Type	Tubular
Technology	Halogen

Physical

MOL	4
MOD	1.25

Additional Information

Warranty	Avg. Rated Hour Limited
----------	-------------------------

Compliance

Safety Listing	Not Listed
Location Rating	Damp
Energy Star	No
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
SDS Sheet	Halogen_Tungsten_Lamp