

# Accent 1-Lt 120V

15241BKT (Textured Black)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_



## Ordering Information

|                    |                |
|--------------------|----------------|
| Product ID         | 15241BKT       |
| Finish             | Textured Black |
| Available Finishes | AZT, BKT       |

## Specifications

|                      |                             |
|----------------------|-----------------------------|
| Material             | Aluminum                    |
| Diffuser Description | Tempered Convex Clear Glass |

## Electrical

|                  |       |
|------------------|-------|
| Voltage          | 120V  |
| Lead Wire Length | 8.00" |

## Qualifications

|              |  |
|--------------|--|
| Safety Rated | Wet  |
| Warranty     | <a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a> |

## Primary Lamping

|                        |              |
|------------------------|--------------|
| Light Source           | Incandescent |
| Lamp Included          | Not Included |
| # of Bulbs/LED Modules | 1            |
| Max or Nominal Watt    | 75W          |
| Socket Wire            | 125          |
| Socket Type            | Medium       |
| Lamp Type              | R30          |

## Dimensions

|        |       |
|--------|-------|
| Height | 6.75" |
| Length | 9.00" |
| Width  | 5.00" |

## Alternate Lamps

| Lamp Included | Bulb Listing | Light Source | Max Wattage/Range | Bulb Product ID | Dimming |
|---------------|--------------|--------------|-------------------|-----------------|---------|
| No            | Alternate    | INCA         | 75W               |                 |         |