



GE
Lighting

13829 - null

LED7DRS20F827

Product Photo



GENERAL CHARACTERISTICS

Rated Life (Hours)	25000 h
10 Digit U	4316813829
Lamp Count	1
Requested Structure	Carton
Bulb Shape	R20

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	0 cd
Nominal Initial Lumen per Watt	67
Initial Lumens-nominal	470 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	13829
Description	LED7DRS20F827
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168138291
Standard Package GTIN	00043168138291
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168138291
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168138291
Standard Package GTIN	10043168138298
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168138291

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	7 W