

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_



Halogen

# P5200-20

## Linear Path Light

Low profile path light in a cast bronze construction. Wide beam illumination with etched glass spread lens. Surface mount on ground. Complete with stake, 18w T5 wedge base lamp and 1/2 IP. This low voltage path light has minimal visibility perfect for walkways. Units must be wired to a 12V transformer with proper capacity.

- Antique Bronze finish.
- Low profile path light in a cast bronze construction.
- Wide beam illumination with etched glass spread lens.
- Complete with stake, 18w T5 wedge base lamp and 1/2 IP.
- Units must be wired to an approved 12V transformer of proper capacity.

Width: 6-3/4"  
Height: 1-5/8"

Glass  
Width: 2-9/16"  
Height: 1-3/16"

**Category:** Landscape

**Finish:** Antique Bronze (Painted)

**Construction:** Cast bronze construction

**Glass/Shade:** Etched glass lens

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
1/2 IP thread, ground stake included mounted	Pre-wired 6" of wire supplied 12 V	Quantity: One 18w max. T5 wedge base(included) Wedge base ceramic socket	UL-CUL Wet location listed 1 year warranty