

# Top-Bite Saddle Type Connectors

## 90° with Insulated Throat

### Features

- With insulated throat
- Male hub threads - NPSM
- One piece malleable construction affording extra strength
- Dual gripping saddle clamps
- Saddle clamps ride up and down on screw for ease of installation
- Tri combo head screw



### Applications


- To connect Flex, AC, and MC cables to a box or enclosure

### Standard Material

- Malleable iron
- Steel locknuts
- Steel clamps

### Standard Finish

- Zinc plated



Catalog Number	UPC	Size	KO	Unit Carton	Ship Case	Weight/Case	Opening Min.	Cable Max.	A	Inches B	C
<b>490TBS</b>	85186	<b>3/8"</b>	1/2"	50	300	54	.437	.656	1.75	2.06	1.00
<b>491TBS</b>	85187	<b>1/2"</b>	1/2"	25	150	43	.750	.937	2.13	2.26	1.25
<b>492TBS</b>	85188	<b>3/4"</b>	3/4"	20	120	43	.906	1.13	2.50	2.50	1.38
<b>493TBS</b>	85189	<b>1"</b>	1"	5	60	34	1.25	1.47	2.81	2.88	1.69