

Item # K9401-L-MW	UPC Code: 706411037788
Product Family Name:	Finish: Mossoro Walnut™
Category: LIGHT KITS	Category Type: Light Kit
Certification E75795	
Patents:	
Notes:	



Image File Name: **K9401-L-MW.jpg**



MEASUREMENTS

Width: 10.5	Length: 10.5	Height: 5.5	Extension:
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7"	Chain Length:	Safety Cable Included: No	Net Weight: 3.13
Canopy Width:	Canopy Height:	Canopy Length:	Center to Bottom:
Backplate Width:	Backplate Height:	Center to Top:	

LAMPING

No. of Bulbs: 2	Light Type: SEMI SPIRAL, 13W, SELF-BALLAST, GU24	Light Kit Optional: No		
Max Bulb Wattage: 13	Socket: GU24			
Integrated Light Kit: No	Dimmable: No	Ballast:	Rated Life Hours:	Uplight: No
Bulb/LED Included: Yes	Color Temp.: CRI:		Initial Lumens:	Delivered Lumens:

GLASS

Description: Opal	Material:	
Part No.:	Quantity:	
Width: 10.0	Height: 3.75	Length: 10.0



CONTROLS

Pull Chain Control: No	Works with Remote Control: No	Works with Wall Control: No
Reversible: No	Included Remote Control:	Included Wall Control:
Smart Control: No	Compatible Remote Control(s):	Compatible Wall Control(s):
Integrated Smart Control:		Compatible Smart Control:



SHIPPING

Carton Width: 12.0	Carton Height: 9.5	Carton Length: 12.0
Carton Weight: 4.09	Carton Cubic Feet: 0.792	Small Package Shippable: Yes
Master Pack Width: 12.75	Master Pack Height: 28.75	Master Pack Length: 24.75
Master Pack Weight: 26.884	Master Cubic Feet: 5.25	Multi-Pack: Master Pack: 1 6



Wet Location



UL Listed

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.

Rev 11.06.2019 09:59 AM