



Powering Business Worldwide

pe.eaton.com

Type GHB Bolt-On Panelboard Circuit Breaker

GHB1045

UPC:786679006382

Dimensions:

- **Height:** 3.5 IN
- **Length:** 6 IN
- **Width:** 1.75 IN

Weight:.9 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Molded case circuit breaker
- **Amperage Rating:** 45A
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 277 Vac, 125 Vdc
- **Mounting:** Bolt-on
- **Frame Size:** G-frame
- **Series:** Series C
- **Trip Type:** Non-interchangeable thermal-magnetic

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Series C GB/GHB/GDB Circuit Breakers - IL](#)
- [MOEM MCCB Product Selection Guide](#)
- [G-frame Molded Case Circuit Breaker Drawing](#)
- [Series C G-Frame Time Current Curves](#)
- [Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve](#)

Certifications:

- UL Listed



Product compliance:

- Federal Specifications Classification W-C375B

© 2016 Eaton. All rights reserved.