



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Thermal-Magnetic Circuit Breaker

BAB3050HS

UPC:786679509678

Dimensions:

- **Height:** 3.5 IN
- **Length:** 3.6 IN
- **Width:** 4 IN

Weight:1.3 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag
- **Special Features:** 120V, 208V, 240V shunt trip
- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Mounting:** Bolt-on
- **Trip Type:** Non-Interchangeable
- **Quantity:** Q32
- **Circuit Breaker Type:** BAB

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3050HS](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data



