



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 3-Pole, 240VAC are Circuit Protection Molded Case Circuit Breakers. Type: BL Special Features: Shunt Trip 120V Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240V Amperage Rating: 20A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 3P

| | |
|---------------------------------|-------------------------|
| Number of poles | 3 |
| Suitability for operation | Electrical Distribution |
| Electricity | |
| Continuous current rated value | 20 A |
| Model | |
| Product brand name | SIEMENS |
| Special product feature | Shunt Trip 120V |
| Type of electrical connection | BOLT-ON |
| Mechanical Design | |
| Depth [in] | 5.5 in |
| Design of the product | BL |
| Height [in] | 3.8 in |
| Width [in] | 4.4 in |
| General product approval | |
| Standard | UL 489 |
| last modified: | 04/10/2018 |