



Powering Business Worldwide

pe.eaton.com

Eaton enhanced visible blade single-throw fused safety switch

DH222FRK

UPC:786685176758

Dimensions:

- **Height:** 8.5 IN
- **Length:** 16.5 IN
- **Width:** 9.5 IN

Weight:19 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Enhanced visible blade
- **Type:** Heavy duty fusible safety switch
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Two-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 3, 7.5 hp/10, 15 hp/10 hp (1,3PH @ Std fuse/time delay/250 Vdc)

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH222FRK](#)

Certifications:

- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.