



GE
Lighting

96769 - GE LED Plug-in

LED12G24Q-H/840

- ☞ GE's LED plug-in lamps allow you to replace inefficient CFL 4 pin G24q/GX24 without tools or costly upgrades. Simply plug the replacement lamp into the existing ballast.
- ☞ Uses 50% less energy than CFL (12W LED vs. 26W CFL)
- ☞ These lamps are energy efficient, contain no lead or mercury, and meet the material restriction requirements of RoHS
- ☞ For example, using only 12 watts of energy, save over \$71 in energy costs over the rated life of a lamp versus a standard 26-watt CFL lamp based on \$0.11 per kWh
- ☞ Advanced optics eliminate wasted light to deliver a more targeted beam with fewer lumens (950 vs. 1800)
- ☞ Energy efficiency and long life mean fewer lamp replacements versus CFL light sources
- ☞ Check ballast compatibility at GELighting.com/LED4pin-compatibility

Product Photo



GENERAL CHARACTERISTICS

Base Description	G24Q/GX24
Base Type	4-Pin Plug-in
Body Color	White
Dimmable	No
Primary Application	Indoor Damp
Product Color	White
Product Technology	LED
Rated Life (Hours)	50000 h
Dimmable / Non-Dimmable	No
10 Digit U	4316896769
Lamp Count	1
Life in Years	45.7 yr
Replacement Watts	0 W
Requested Structure	Carton
Estimated Energy Cost per Year	1.45
Base	G24q-4

PHOTOMETRIC CHARACTERISTICS

Lumens per Watt (Efficacy)	83.3 lm
Nominal Initial Lumen per Watt	83.3
Initial Lumens-nominal	1000 lm
Color Rendering Index-CRI	80
Color Temperature	4000 K

PRODUCT INFORMATION

Product Code	96769
Description	LED12G24Q-H/840
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168967693
Standard Package GTIN	10043168967690
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168967693
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168967693
Standard Package GTIN	00043168967693
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168967693

DIMENSIONS

Bulb Max Overall Length-MOL	5.31 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	12 W
---------------------	------

CAUTIONS & WARNINGS

Caution

Risk of Electric Shock

Suitable for damp locations

Direct replacement for 13W/6T4/Q/G24/PH, 18W/7T4/Q/G24/PH, 26W/8T4/Q/G24/PH CFL lamps only

Not for use with dimmers

For use only with compatible magnetic ballasts. See list at: www.gelighting.com/LED2pin-compatibility

If the lamp does not light when the luminaire is energized, remove lamp from luminaire and contact lamp manufacturer or qualified electrician

If the lamp or luminaire exhibits undesirable operation, such as flickering or buzzing, immediately turn off power, remove lamp from luminaire, and contact manufacturer

Not intended for use with emergency exit lights

Do not use where directly exposed to water

Sep 22, 2017 5:26:54 AM For additional information, visit www.gelighting.com