

WALL COLLECTION

Essex Wall



DESCRIPTION


Glass or fabric shade options with minimal metal detail. Provides ambient, up- and down-light. Includes 120 volt, 60 watt G9 base halogen lamp, 120 volt 18 watt GU24 base self-ballasted compact fluorescent lamp or 10 watt, 600 lumen, 2700K LED module. Incandescent version dimmable with standard incandescent dimmer. LED version dimmable with low-voltage electronic dimmer. ADA compliant.

INSTALLATION

This product can mount to either a 4" square electrical box with round plaster ring or an octagonal electrical box (not included). For wall mount use only.

WEIGHT

1.61lb / 0.73kg ±



glass ivory/brown/amber

COLOR OPTIONS



ORDERING INFORMATION

700WSESX COLOR	FINISH	LAMP
SC CLEAR	Z ANTIQUE BRONZE	INCANDESCENT 120V
FC FABRIC DESERT CLAY	C CHROME	-CF COMPACT FLUORESCENT 120V
FW FABRIC WHITE	S SATIN NICKEL	-LED LED 2700K 120V
GA GLASS BEACH AMBER		-LED277 LED 2700K 277V
IBA GLASS IVORY/BROWN/AMBER		
GS GLASS SAND		
GW GLASS SURF WHITE		
PB SHELL BROWN		
PN SHELL NATURAL		
PW SHELL WHITE		
SK SMOKE		
SH WHEAT		

TECH LIGHTING®
 7400 Linder Avenue T 847.410.4400
 Skokie, Illinois 60077 F 847.410.4500
Tech Lighting, L.L.C.

700WSESX _____

FIXTURE TYPE: _____

JOB NAME: _____

NOTES: _____

