


## RAS12 - R SERIES 12" ANGLE SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and arms below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41
- Compatible with wire guard: RWG12



### Dimensions

Width	12"
Height	12½"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>BP</b> - Black Porcelain <b>GA</b> - Galvanized <b>GY</b> - Gray <b>NB</b> - Navy Blue <b>NC</b> - Natural Copper <b>SB</b> - Satin Black <b>SFP</b> - Sea Foam Porcelain <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White <b>WP</b> - White Porcelain
Material	Metal

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------


### Item Number

SKU	RAS12
-----	-------

## RAS10 - R SERIES 10" ANGLE SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and goose neck below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41
- Compatible with wire guard: RWG10



### Dimensions

Width	10"
Height	11"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>BP</b> - Black Porcelain <b>GA</b> - Galvanized <b>GY</b> - Gray <b>NB</b> - Navy Blue <b>NC</b> - Natural Copper <b>SB</b> - Satin Black <b>SFP</b> - Sea Foam Porcelain <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White <b>WP</b> - White Porcelain
Material	Metal

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------

### Item Number


SKU	RAS10
-----	-------

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RDBS12 - R SERIES 12" DEEP BOWL SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and arms below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41
- Compatible with wire guard: RWG17



### Dimensions

Width	12"
Height	11½"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze
	<b>GA</b> - Galvanized
	<b>GY</b> - Gray
	<b>NB</b> - Navy Blue
	<b>SB</b> - Satin Black
	<b>SG</b> - Satin Green
	<b>SR</b> - Satin Red
	<b>WH</b> - White

Material	Metal
----------	-------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------


### Item Number

SKU	RDBS12
-----	--------

## RDBS10 - R SERIES 10" DEEP BOWL SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and goose neck below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41
- Compatible with wire guard: RWG14



### Dimensions

Width	10"
Height	11"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze
	<b>GA</b> - Galvanized
	<b>GY</b> - Gray
	<b>NB</b> - Navy Blue
	<b>SB</b> - Satin Black
	<b>SG</b> - Satin Green
	<b>SR</b> - Satin Red
	<b>WH</b> - White

Material	Metal
----------	-------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------

### Item Number


SKU	RDBS10
-----	--------

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RES12 - R SERIES 12" EMBLEM SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and arms below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41
- Compatible with wire guard: RWG17



Accepts 3/4" stem

### Dimensions

Width	12"
Height	14½"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze
	<b>GA</b> - Galvanized
	<b>SB</b> - Satin Black
	<b>SG</b> - Satin Green
	<b>SR</b> - Satin Red
	<b>WH</b> - White
Material	Metal

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------


### Item Number

SKU	RES12
-----	-------

## RES10 - R SERIES 10" EMBLEM SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and goose neck below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41
- Compatible with wire guard: RWG14



Accepts 3/4" stem

### Dimensions

Width	10"
Height	13"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze
	<b>GA</b> - Galvanized
	<b>SB</b> - Satin Black
	<b>SG</b> - Satin Green
	<b>SR</b> - Satin Red
	<b>WH</b> - White
Material	Metal

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------

### Item Number


SKU	RES10
-----	-------

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RMWHS17 - R SERIES 17" MODIFIED WAREHOUSE SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and arms below:

- Compatible with AL- Aluminum downrods: RS1, RS2, and RS3
- Compatible with AL- Aluminum goose necks: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41



Accepts 3/4" stem

### Dimensions

Width	9 1/4"
Height	17"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze
	<b>BA</b> - Brushed Aluminum
	<b>SB</b> - Satin Black
	<b>SG</b> - Satin Green
	<b>SR</b> - Satin Red
	<b>WH</b> - White

Material	Metal
----------	-------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------


### Item Number

SKU	RMWHS17
-----	---------

## RMWHS14 - R SERIES 14" MODIFIED WAREHOUSE SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and goose neck below:

- Compatible with AL- Aluminum downrods: RS1, RS2, and RS3
- Compatible with AL- Aluminum goose necks: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41



Accepts 3/4" stem

### Dimensions

Width	8 1/4"
Height	14"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze
	<b>BA</b> - Brushed Aluminum
	<b>SB</b> - Satin Black
	<b>SG</b> - Satin Green
	<b>SR</b> - Satin Red
	<b>WH</b> - White

Material	Metal
----------	-------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------

### Item Number

SKU	RMWHS14
-----	---------


**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RWHS17 - R SERIES 17" WAREHOUSE SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck.

Please see compatible downrods and arms below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41
- Compatible with wire guard: RWG17



Accepts 3/4" stem

### Dimensions

Width	9 1/4"
Height	17"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>BP</b> - Black Porcelain <b>GA</b> - Galvanized <b>GY</b> - Gray <b>NB</b> - Navy Blue <b>NC</b> - Natural Copper <b>SB</b> - Satin Black <b>SFP</b> - Sea Foam Porcelain <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White <b>WP</b> - White Porcelain
Material	Metal

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------

### Item Number


SKU	RWHS17
-----	--------

## RWHS14 - R SERIES 14" WAREHOUSE SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck.

Please see compatible downrods and goose neck below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41
- Compatible with wire guard: RWG14



Accepts 3/4" stem

### Dimensions

Width	8 1/4"
Height	14"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>BP</b> - Black Porcelain <b>GA</b> - Galvanized <b>GY</b> - Gray <b>NB</b> - Navy Blue <b>NC</b> - Natural Copper <b>SB</b> - Satin Black <b>SFP</b> - Sea Foam Porcelain <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White <b>WP</b> - White Porcelain
Material	Metal

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------

### Item Number


SKU	RWHS14
-----	--------

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RRRS18 - R SERIES 18" RAILROAD SHADE


This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and arms below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41



Accepts 3/4" stem

Inside Etched Glass and Glass Guard Included



### Dimensions

Width	18"
Height	10"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>CP</b> - Copper <b>GA</b> - Galvanized <b>SB</b> - Satin Black
----------	--

Material	Metal
----------	-------

### Glass

Glass	Inside Etched Glass
-------	---------------------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------


### Item Number

SKU	RRRS18
-----	--------

## RRRS14 - R SERIES 14" RAILROAD SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and goose neck below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41



Accepts 3/4" stem

Inside Etched Glass and Glass Guard Included

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

### Dimensions

Width	9 1/2"
Height	14"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>CP</b> - Copper <b>GA</b> - Galvanized <b>SB</b> - Satin Black
----------	--

Material	Metal
----------	-------

### Glass

Glass	Inside Etched Glass
-------	---------------------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------


### Item Number

SKU	RRRS14
-----	--------

## RRWS18 - R SERIES 18" RADIAL WAVE SHADE


This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and arms below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41



Accepts 3/4" stem

Inside Etched Glass and Glass Guard Included



### Dimensions

Width	18"
Height	11 1/4"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>SB</b> - Satin Black <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White
----------	---

Material	Metal
----------	-------

### Glass

Glass	Inside Etched Glass
-------	---------------------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------


### Item Number

SKU	RRWS18
-----	--------

## RRRS15 - R SERIES 15" RADIAL WAVE SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck. Please see compatible downrods and goose neck below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41



Accepts 3/4" stem

Inside Etched Glass and Glass Guard Included

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

### Dimensions

Width	15"
Height	11 1/4"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>SB</b> - Satin Black <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White
----------	---

Material	Metal
----------	-------

### Glass

Glass	Inside Etched Glass
-------	---------------------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------

### Item Number


SKU	RRWS15
-----	--------

## RRWS12 - R SERIES 12" RADIAL WAVE SHADE

This item can be converted to a pendant or wall sconce with purchase of separate compatible downrod or goose neck.


Please see compatible downrods and arms below:

- Compatible downrods: RS1, RS2, and RS3
- Compatible with arms: RGN10, RGN12, RGN13, RGN15, RGN22, RGN23, RGN24, RGN30, and RGN41



Accepts 3/4" stem

Inside Etched Glass and Glass  
Guard Included



### Dimensions

Width	12"
Height	11 1/4"
Wire	100"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>SB</b> - Satin Black <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White
Material	Metal

### Glass

Glass	Inside Etched Glass
-------	---------------------

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification

UL Listed	Wet Location
-----------	--------------

### Item Number


SKU	RRWS12
-----	--------

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.



## R SERIES OPTIONS

### GOOSE NECKS - (WALL MOUNT)




ID: 3/4"

#### FINISHES

- ABR - Architectural Bronze
- AL - Aluminum
- ASB - Aluminum Painted Satin Black
- BP - Black Porcelain
- GA - Galvanized
- GY - Gray
- NB - Navy Blue
- NC - Natural Copper
- SB - Satin Black
- SFP - Sea Foam Porcelain
- SG - Satin Green
- SR - Satin Red
- WH - White
- WP - White Porcelain

### STEMS AND CANOPY KITS - (CEILING MOUNT)




ID: 3/4"

#### FINISHES

- ABR - Architectural Bronze
- CP - Copper
- GA - Galvanized
- GY - Gray
- NB - Navy Blue
- SB - Satin Black
- SG - Satin Green
- SR - Satin Red
- WH - White

### STEM CONNECTORS




Accepts 3/4" stem


#### FINISHES

- ABR - Architectural Bronze
- AL - Aluminum
- CP - Copper
- GA - Galvanized
- GY - Gray
- NB - Navy Blue
- SB - Satin Black
- SG - Satin Green
- SR - Satin Red
- WH - White

### WALL MOUNT SWIVELS



### WIRE GUARDS



#### FINISHES


- ABR - Architectural Bronze
- GA - Galvanized
- GY - Gray
- NB - Navy Blue
- SB - Satin Black
- SG - Satin Green
- SR - Satin Red
- WH - White

### LED MODULE

#### RLED24W

This accessory is only compatible for the Warehouse Shade (i.e. RWHS14 & RWHS17).

#### RLED24W




1920 Lumens  
3000K  
CRI 90  
Dimmable

## R SERIES OPTIONS

### 1 LIGHT POST ADAPTERS

- Will work with any RLM shade
- Designed to fit standard 3" posts and pier mount bases
- Unique stem hung design does not require pipe sealant compound on fittings.
- 3/4" inner diameter rigid conduit or water pipe may be substituted for stems or goose necks.

RPAS



### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>AL</b> - Aluminum <b>CP</b> - Copper <b>GA</b> - Galvanized <b>GY</b> - Gray <b>NB</b> - Navy Blue <b>SB</b> - Satin Black <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White
Material	Cold Rolled Steel, Die Cast Zinc

### Certification

UL Listed Wet Location


### Item Number

SKU RPAS

### 2 LIGHT POST ADAPTERS

- Will work with any RLM shade
- Designed to fit standard 3" posts and pier mount bases
- Unique stem hung design does not require pipe sealant compound on fittings.
- 3/4" inner diameter rigid conduit or water pipe may be substituted for stems or goose necks.

RPAD



### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>AL</b> - Aluminum <b>CP</b> - Copper <b>GA</b> - Galvanized <b>GY</b> - Gray <b>NB</b> - Navy Blue <b>SB</b> - Satin Black <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White
Material	Cold Rolled Steel, Die Cast Zinc


### Certification

UL Listed Wet Location


### Item Number

SKU RPAD

## RWHC17 - R SERIES 17" FABRIC CORD HUNG WAREHOUSE SHADE



### Options:



### Dimensions

Width	9 1/4"
Height	17"
Wire	144"

### Finish & Material

Finishes	<b>NC</b> - Natural Copper <b>PN</b> - Polished Nickel
Material	Natural Copper Steel

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No


### Certification

UL Listed	Damp Location
-----------	---------------


### Item Number

SKU	RWHC17
-----	--------

## RWHC14 - R SERIES 14" FABRIC CORD HUNG WAREHOUSE SHADE



### Options:



### Dimensions

Width	8 1/4"
Height	14"
Wire	144"

### Finish & Material

Finishes	<b>NC</b> - Natural Copper <b>PN</b> - Polished Nickel
Material	Natural Copper Steel

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification


UL Listed	Damp Location
-----------	---------------

### Item Number



SKU	RWHC14
-----	--------

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RWHC17 - R SERIES 17" CORD HUNG WAREHOUSE SHADE



### Options:



### Dimensions

Width	9 1/4"
Height	17"
Wire	144"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>GA</b> - Galvanized <b>GY</b> - Gray <b>NB</b> - Navy Blue <b>SB</b> - Satin Black <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White
Material	Steel

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No


### Certification

UL Listed	Damp Location
-----------	---------------



### Item Number

SKU	RWHC17
-----	--------

## RWHC14 - R SERIES 14" CORD HUNG WAREHOUSE SHADE



### Options:



### Dimensions

Width	8 1/4"
Height	14"
Wire	144"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>GA</b> - Galvanized <b>GY</b> - Gray <b>NB</b> - Navy Blue <b>SB</b> - Satin Black <b>SG</b> - Satin Green <b>SR</b> - Satin Red <b>WH</b> - White
Material	Steel

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	200W
Voltage	120V
Bulbs Included	No

### Certification


UL Listed	Damp Location
-----------	---------------

### Item Number

SKU	RWHC14
-----	--------


**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RDBC12 - R SERIES 12" CORD HUNG DEEP BOWL SHADE



### Options:

#### RWG12



#### FINISHES

**ABR** - Architectural Bronze  
**GA** - Galvanized  
**GY** - Gray  
**NB** - Navy Blue  
**SB** - Satin Black  
**SG** - Satin Green  
**SR** - Satin Red  
**WH** - White

### Dimensions

Width 12"  
 Height 11½"  
 Wire 144"

### Finish & Material

Finishes **ABR** - Architectural Bronze  
**GA** - Galvanized  
**GY** - Gray  
**NB** - Navy Blue  
**SB** - Satin Black  
**SG** - Satin Green  
**SR** - Satin Red  
**WH** - White

### Wattage

Bulbs 1-Medium A21  
 Watts per Bulb 200W  
 Voltage 120V  
 Bulbs Included No


### Certification

UL Listed Damp Location

### Item Number


SKU RDBC12

## RDBC10 - R SERIES 10" CORD HUNG DEEP BOWL SHADE



### Options:

#### RWG10



#### FINISHES

**ABR** - Architectural Bronze  
**GA** - Galvanized  
**GY** - Gray  
**NB** - Navy Blue  
**SB** - Satin Black  
**SG** - Satin Green  
**SR** - Satin Red  
**WH** - White

### Dimensions

Width 10"  
 Height 11"  
 Wire 144"

### Finish & Material

Finishes **ABR** - Architectural Bronze  
**GA** - Galvanized  
**GY** - Gray  
**NB** - Navy Blue  
**SB** - Satin Black  
**SG** - Satin Green  
**SR** - Satin Red  
**WH** - White

Material Steel

### Wattage

Bulbs 1-Medium A21  
 Watts per Bulb 200W  
 Voltage 120V  
 Bulbs Included No

### Certification

UL Listed Damp Location

### Item Number


SKU RDBC10

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.


## RRRC18 - R SERIES 18" CORD HUNG RAILROAD SHADE



Inside Etched Glass and Wire  
Guard Included



### Options:



### Dimensions

Width	18"
Height	10"
Wire	144"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>CP</b> - Copper <b>GA</b> - Galvanized <b>SB</b> - Satin Black
----------	--

Material	Steel
----------	-------

### Glass & Wire Guard

Glass	Inside Etched
Wire Guard	Metal

### Wattage

Bulbs	1-Medium A19
Watts per Bulb	100W
Voltage	120V

### Certification

UL Listed	Damp Location
-----------	---------------


### Item Number

SKU	RRRC18
-----	--------


## RRRC14 - R SERIES 14" CORD HUNG RAILROAD SHADE



Inside Etched Glass and Wire  
Guard Included



### Options:



### Dimensions

Width	14"
Height	9½"
Wire	144"

### Finish & Material

Finishes	<b>ABR</b> - Architectural Bronze <b>CP</b> - Copper <b>GA</b> - Galvanized <b>SB</b> - Satin Black
----------	--

Material	Steel
----------	-------

### Glass & Wire Guard

Glass	Inside Etched
Wire Guard	Metal

### Wattage

Bulbs	1-Medium A19
Watts per Bulb	100W
Voltage	120V

### Certification


UL Listed	Damp Location
-----------	---------------

### Item Number


SKU	RRRC14
-----	--------

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RRWC18 - R SERIES 18" CORD HUNG RADIAL WAVE SHADE



### Options:



### Dimensions

Width	18"
Height	11 1/4"
Wire	144"

### Finish & Material

Finishes	CP - Copper GA - Galvanized Steel
Material	Steel

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	100W
Voltage	120V

### Glass & Wire Guard

Glass	Inside Etched
Wire Guard	Metal


### Certification

UL Listed	Damp Location
-----------	---------------


### Item Number

SKU	RRWC18
-----	--------

## RRWC15 - R SERIES 15" CORD HUNG RADIAL WAVE SHADE



### Options:



### Dimensions

Width	15"
Height	11 1/4"
Wire	144"

### Finish & Material

Finishes	CP - Copper GA - Galvanized Steel
Material	Steel

### Glass & Wire Guard

Glass	Inside Etched
Wire Guard	Metal

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	100W
Voltage	120V


### Certification

UL Listed	Damp Location
-----------	---------------


### Item Number

SKU	RRWC15
-----	--------

## RRWC12 - R SERIES 12" CORD HUNG RADIAL WAVE SHADE



### Options:



### Dimensions

Width	12"
Height	11 1/4"
Wire	144"

### Finish & Material

Finishes	CP - Copper GA - Galvanized Steel
Material	Steel

### Glass & Wire Guard

Glass	Inside Etched
Wire Guard	Metal

### Wattage

Bulbs	1-Medium A21
Watts per Bulb	100W
Voltage	120V

### Certification


UL Listed	Damp Location
-----------	---------------

### Item Number

SKU	RRWC12
-----	--------

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## 5440 - R SERIES 10" NATURAL COPPER WALL BRACKET



W: 10"  
H: 11"  
Ext: 12½"

Removable Stainless Steel  
Wire Guard Included

### Dimensions

Width 10"  
Height 11"  
Extension 12½"

### Finish & Material

Finishes **ABR** - Architectural Bronze  
Material Aluminum

### Wattage

Bulbs 1-Medium A19  
Watts per Bulb 100W  
Voltage 120V


### Certification

UL Listed Wet Location

### Item Number

SKU 5440

## 5441 - R SERIES 10" ALUMINUM WALL BRACKETS



W: 10"  
H: 11"  
Ext: 12½"

Removable Wire Guard  
Included

### Dimensions

Width 10"  
Height 11"  
Extension 12½"

### Finish & Material

Finishes **ABR** - Architectural Bronze  
**BA** - Brushed Aluminum  
**SB** - Satin Black

Material Aluminum

### Wattage

Bulbs 1-Medium A19  
Watts per Bulb 100W  
Voltage 120V


### Certification

UL Listed Wet Location

### Item Number

SKU 5441

## 5451 - R SERIES 10" ALUMINUM WALL BRACKETS



W: 10"  
H: 11"  
Ext: 12½"

### Dimensions

Width 10"  
Height 11"  
Extension 12½"

### Finish & Material

Finishes **ABR** - Architectural Bronze  
**BA** - Brushed Aluminum  
**SB** - Satin Black

Material Aluminum

### Glass

Glass Clear Prismatic

### Wattage

Bulbs 1-Medium A19  
Watts per Bulb 100W  
Voltage 120V

### Certification

UL Listed Wet Location


### Item Number

SKU 5451

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.



## 5393-NC - R SERIES 9" NATURAL COPPER WALL BRACKET



W: 8½"  
H: 11½"  
Ext: 11"

Removable Wire Guard and  
Clear Non-Ribbed Glass  
Included

### Dimensions

Width 8½"  
Height 11½"  
Extension 11"

### Finish & Material

Finishes **NC** - Natural Copper

Material Natural Copper

### Glass and Wire Guard

Glass Clear  
Wire Guard Stainless Steel

### Wattage

Bulbs 1-Medium A19  
Watts per Bulb 100W  
Voltage 120V


### Certification

UL Listed Wet Location

### Item Number

SKU 5393-NC

## 5390 - R SERIES 9" WALL BRACKETS



W: 8½"  
H: 11½"  
Ext: 11"

Removable Wire Guard  
Included

### Dimensions

Width 8½"  
Height 11½"  
Extension 11"

### Finish & Material

Finishes **ABR** - Architectural Bronze

**GA** - Galvanized

**SB** - Satin Black

Material Cold Rolled Steel &  
Die-Cast Zinc

### Glass and Wire Guard

Glass Clear  
Wire Guard Steel

### Wattage

Bulbs 1-Medium A19  
Watts per Bulb 100W  
Voltage 120V

### Certification

UL Listed Wet Location

### Item Number

SKU 5390




RGCNR RGCR

RGCNR and RGCR glass may be used as optional clear glass. Must be purchased separately.

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.

## RWHWB8-NC - R SERIES 8" NATURAL COPPER WALL BRACKET



W: 8"  
H: 11¼"  
Ext: 11"

Removable Stainless Steel  
Wire Guard Included

### Dimensions

Width 8"  
Height 11¼"  
Extension 11"

### Finish & Material

Finishes **NC** - Natural Copper  
Material Natural Copper

### Wire Guard

Wire Guard Stainless Steel

### Wattage

Bulbs 1-Medium A19  
Watts per Bulb 100W  
Voltage 120V


### Certification

UL Listed Wet Location

### Item Number

SKU RWHWB8-NC

## RWHWB8 - R SERIES 8" WALL BRACKETS



W: 8"  
H: 11¼"  
Ext: 11"

Removable Wire Guard  
Included

### Dimensions

Width 8"  
Height 11¼"  
Extension 11"

### Finish & Material

Finishes **ABR** - Architectural Bronze  
**GA** - Galvanized  
**SB** - Satin Black  
**SG** - Satin Green  
**SR** - Satin Red  
**WH** - White

Material Cold Rolled Steel &  
Die-Cast Zinc

### Wire Guard

Wire Guard Steel

### Wattage

Bulbs 1-Medium A19  
Watts per Bulb 100W  
Voltage 120V

### Certification

UL Listed Wet Location

### Item Number

SKU RWHWB8

**Note:** All finishes on outdoor lighting must be properly maintained and treated. Therefore, we suggest cleaning with a regular application of finish preserving & renewing products such as Rejuvenate.