


Model: H/L/J-LED202

AC LED Track Luminaire

WAC LIGHTING

Responsible Lighting®



Fixture Type:

Catalog Number:

Project:

Location:

PRODUCT DESCRIPTION


LED202 track luminaire offers driverless AC LED technology and easy change of beam angles in field. Superior light output in a small, unobtrusive design. The high output LEDs outperform halogen 50W MR16. Developed for upscale residential and commercial environments.

FEATURES

- Driverless AC LED technology
- Compact integrated design
- Easy change of beam angles in field
- Outperforms halogen 50W MR16
- Consistent high quality beam pattern
- Accommodates 1 lens accessory
- 360° horizontal and 90° vertical aiming
- 50,000 hour rated life
- 5 year WAC Lighting product warranty

BEAMSHIFT™ TECHNOLOGY

LED202 track luminaires come with BeamShift™, allowing in-field change of beam angle simply by changing the location of the lens with a simple flat-head screwdriver.



Flood 40° Configuration
Convex Lens located behind the spacer

Spot 25° Configuration
Convex Lens located in front of the spacer.

SPECIFICATIONS

Construction: Die-cast aluminum with removable PC lens cap for easy change of lenses or accessories

Finish: Black (BK) and White (WT) powder coat paint.

Driver: Input voltage: 120VAC 50/60Hz.

Light Source: High Voltage AC LED module.

Dimming: Dims to 10%-100% with electronic low voltage (ELV) dimmer. Compatible with LUTRON SELV-300P, DVELV-300P

Standards: ETL & cETL Listed. Energy Star Rated.

ORDER NUMBER

| Track System | Model | Finish | Voltage | Color Temp | Power | CRI | Beam | Lumens | Efficacy |
|--|-----------|----------|---------|------------|-------|-----|------|---------|----------|
| H H Track L L Track J J/J2 Track | LED202-30 | BK Black | 120V | 3000K | 15W | 85 | 25° | 540 | 36 Lm/W |
| WT White | | 40° | | | | | 660 | 44 Lm/W | |

FINISHES



- **LED202-30** -

Example: H-LED202-30-WT

LENSES & ACCESSORIES

| Model | Color |
|--------------------|------------|
| LENS-16 Color Lens | AMB Amber |
| | BLU Blue |
| | GRN Green |
| | RED Red |
| | YEL Yellow |

WAC Lighting
www.waclighting.com
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive • Port Washington, NY 11050
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center
1750 Archibald Avenue • Ontario, CA 91760
Phone (800) 526.2588 • Fax (800) 526.2585

Model: H/L/J-LED202

AC LED Track Luminaire

WAC LIGHTING

Responsible Lighting®

APPLICATION PERFORMANCE – 3000K



0° Aiming Angle (ceiling to floor)

LED202-30 25° beam

| Distance | FC | L | W |
|----------|----|-----|-----|
| 4 ft | 75 | 1.8 | 1.8 |
| 6 ft | 33 | 2.7 | 2.7 |
| 8 ft | 19 | 3.5 | 3.5 |
| 10 ft | 12 | 4.4 | 4.4 |

LED202-30 40° beam

| FC | L | W |
|----|-----|-----|
| 60 | 2.9 | 2.9 |
| 27 | 4.4 | 4.4 |
| 15 | 5.8 | 5.8 |
| 10 | 7.3 | 7.3 |



45° Aiming Angle (ceiling to wall)


LED202-30 25° beam

| Distance | FC | L | W |
|----------|----|-----|-----|
| 4 ft | 26 | 3.7 | 2.5 |
| 6 ft | 12 | 5.6 | 3.8 |
| 8 ft | 7 | 7.5 | 5.0 |
| 10 ft | 4 | 9.3 | 6.3 |

LED202-30 40° beam

| FC | L | W |
|----|------|------|
| 21 | 6.7 | 4.1 |
| 9 | 10.1 | 6.2 |
| 5 | 13.4 | 8.2 |
| 3 | 16.8 | 10.3 |

PHOTOMETRY



— 40°
- - - 25°

WAC Lighting
www.waclighting.com
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive • Port Washington, NY 11050
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center
1750 Archibald Avenue • Ontario, CA 91760
Phone (800) 526.2588 • Fax (800) 526.2585