




**PRODUCT DESCRIPTION**

Maxim Lighting's Dover VX Collection is made with Vivex, a material twice the strength of resin, is non-corrosive, UV resistant and backed with a 5-Year Limited Warranty. Dover VX features our Bronze finish and Seedy glass.



\*height from center of outlet to the top of the fixture

**MEASUREMENTS**

- DIMENSION : 12" W x 31.5" H x 15.5" Ext
- BACK PLATE : 7" W x 15.75" H x 17.5" HCO
- HANGING WEIGHT : 20.02 lb

**LAMPING**

- INPUT VOLTAGE : 120V
- BULB : 3 x 40W Incandescent E12 Candelabra , 120W Total
- BULB INCLUDED : (Not Included)
- DIMMABLE : Yes

**FINISHES OPTION**

- Bronze

**GLASS**

Seedy CD

**MATERIAL**

Vivex Resin Composite, Glass

**RATINGS**

cETLus  
Wet Location



**ADDITIONAL**

OPERATING TEMPERATURE:  
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.



**WESTERN DISTRIBUTION CENTER (HEADQUARTER)**  
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

**EASTERN DISTRIBUTION CENTER**  
4200 SHIRLEY DR. | ATLANTA, GA 30336

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com