



ACO AL OFFSET PIN



- UL486A/B Listed and CSA Certified.
- Rated for 600 Volts and 90° C.
- Dual Rated for Aluminum and Copper Conductor.
- Stranded Class B & C concentric, compressed and unidirectional lay compact
- Rated for full ampacity of incoming conductor.
- Manufactured from high strength aluminum alloy.
- Pin is knurled and off center.
- Chamfered barrel and prefilled with De-Ox.
- Clearly marked with conductor size and die index.
- Marked with number and location of crimps and Color Coded.
- All supplied with insulating cover except ACO-1000.
- ACO-1000 is range taking.
- ACO-1000 must be applied with Dieless Tools Only.
- Coverage for 900 compact aluminum in the ACO-750 when using HK12ID & EK12ID tools only.
- Refer to Tool & Die Charts under Reference Tab for listed Tools.
- UL File # E62525

Item ID	Conductor Size	Die Index Number	Color Code	Pin Diameter	Pin Length	Barrel Length	Cover Length	Approximate Pin Size	Standard Package	NAED/UPC Number
ACO-3/0	3/0 AWG	12	WHITE	0.3700	1.2200	1.3700	2.0000	1/0	10	0783669009521