



Rigid/IMC Conduit Fittings-Hazardous Location T&B Catalog Number:

UPC Number: UNF 205-TB
78621097015
Status: Active
Description:

3/4 in. UNF Female Union, Steel-electro galvanized, 3 piece. For hazardous and non-hazardous locations.

Application

To connect conduit to conduit, or to provide a means for future modification of the conduit system.

General

Trade Size (inches)	3/4
Material	Steel
Finish	Electrogalvanized

Dimension Information

Overall Length (inches)	2 1/8
Overall Diameter (inches)	1 13/16

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	5
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	60 lbs. per 100

Notes

Class I, Div. 1 & 2, Groups B, C, D - Explosionproof
Class II, Div. 1, Groups E, F, G - Dust-Ignitionproof
Class III, Div. 1 & 2 - Raintight

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 193396

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com