



CUTTER,CABLE-RATCHET

Ratchet Cable Cutter (2.4 lbs/1.1 kg)

Cat No: 45207

UPC No: 783310452072

Description

- Simple, one-hand operation
- Exclusive two-speed ratcheting mechanism adjusts for light/heavy cutting
- Well-suited for tight working spaces
- Blades can be opened mid-cycle
- Available with cushioned handles or with 1000V insulated cushioned handles

Specifications

- Application : For Tight Working Spaces
- Cutting Capacity Of Aluminum : 1000.000 KCMIL (MCM) (500.000SQ-MM) Maximum Use, 750.000 KCMIL (MCM) (400.000 SQ-MM) Frequent Use
- Cutting Capacity Of Communication Cables : 2.000 IN (51.000 MM) Diameter Maximum Use
- Cutting Capacity Of Copper : 750 KCMIL (MCM) (400.000 SQ-MM) Maximum Use, 600 KCMIL (MCM) (300.000 SQ-MM) Frequent Use
- Handle Type : Cushioned Grip
- Jaw Size : 2.000 IN (51.000 MM)
- Overall Length : 11.000 IN (279.000 MM)
- Replacement Part : 45211 Movable Blade, 45228 Fixed Blade And Handle
- Type : Ratchet
- Weight : 2.400 LB (1.100 KG)