

Shrink-Kon[®]

Heavy-Wall Heat-Shrinkable Tubing T&B Catalog Number:



UPC Number: HSC300-600
Status: 78621087211
Description: Active

Heat-Shrinkable HSC Series End Caps for Cable Range 2/0 - 350 MCM, Expanded Diameter 1.5 inch, Length 3.25 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

Features

Provides effective method for sealing cable ends, pipe conduit, etc. Extra thickness at the tip of the end prevents sharp ends of the cable from puncturing the seal.

Resistant to common fluids and solvents.

Adhesive liner provides complete environmental protection and insulation.

General

Style	HSC Series End Caps
Color	Black
Temperature Range	-55°C - 110°C
Shrink Ratio	3:1

Dimension Information

Minimum Expanded I.D. (inches)	1.5
Maximum Recovered I.D. (inches)	0.47
Nominal Recovered Wall (inches)	0.16
Cable Range	2/0 - 350 MCM
Standard Length (inches)	3.25

Specifications

Shrink Temperature	120°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Packaging

T&B Order Multiple	5
T&B Inner Pack	5
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	6.5 lbs. per 100

Application Support

MSDS Number	sds-00046-tb2
T&B Sales Drawings	wsd-000470
T&B Instruction Sheets	ta01621-tb2
Specifications	Available on Website
Overview	Available on Website

Notes

Order multiple is standard package.

Certifications



RoHS Compliance

No

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com