



Measurements:

<u>Height</u>	<u>Width</u>
18.25"	19.00"
<u>Max OAH</u>	
17.70"	
<u>Hanging Weight</u>	
7.48 lb	

Lamping:

Incandescent MB	3,450 Rated Lumens
3.00 60W MB	Color Temperature
180 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
9.11 lb	15.55"	9.06"	16.34"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209025820	Yes	

Finish:

Satin Nickel SN

Glass:

Ice IC

Material:

Steel

Certification:

Dry Location
Location

Additional:

MB (Not Included)