



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
8.00"	19.00"	9.00"
<u>BP Height</u>	<u>BP Width</u>	
5.25"	5.25"	
<u>Hanging Weight</u>		
4.43 lb		

Lamping:

Incandescent MB	3,450 Rated Lumens
3.00 60W MB	Color Temperature
180 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
8.07 lb	10.24"	9.45"	22.05"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209212206	Yes	

Finish:

Satin Nickel SN

Glass:

Ice IC

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB (Not Included)
Lighting Direction: Both