



**PRODUCT DESCRIPTION**

Contemporary collection with sweeping arms and clean lines. Offered in Ice glass and Satin Nickel finish or Wilshire glass and Oil Rubbed Bronze finish.

**FINISHES OPTION**

Oil Rubbed Bronze OI



**GLASS**

Wilshire WS

**MATERIAL**

Steel

**RATINGS**

Dry Location  
Dimmable



**ADDITIONAL**


ADJUSTABLE  
INSTALL UP/DOWN:  
RATED LIFE 2500 Hours  
OPERATING TEMPERATURE:  
-20°C (-4°F), 40°C (104°F)

**MEASUREMENTS**

DIMENSION : 26." L x 26." W x 23.5" H  
CANOPY : 5." W x 1." H x 5." L  
HANGING WEIGHT : 14.3 lb

**LAMPING**

INPUT VOLTAGE : 120V  
LUMENS : 5,750 Rated  
BULB : 5 x 60W (NOT INCLUDED), 300W Total  
DIMMABLE : Dimmable



Always consult a qualified electrician before installing any lighting product.



**WESTERN DISTRIBUTION CENTER (HEADQUARTER)**  
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746  
**EASTERN DISTRIBUTION CENTER**  
4200 SHIRLEY DR. | ATLANTA, GA 30336  
P. 626.956.4200 | F. 626.956.4225 | maximlighting.com