



Measurements:

<u>Height</u>	<u>Width</u>	<u>Length</u>
5.00"	11.00"	48.00"
<u>Max OAH</u>		
5.00"		
<u>Hanging Weight</u>		
9.92 lb		

Lamping:

Fluorescent Med Bi Pin T8	5,600 Rated Lumens
2.00 32W Med Bi Pin T8	3000 Color Temperature
64 total watt	20,000 Rated Life
Dimmable : No	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
12.13 lb	12.01"	7.68"	53.15"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209022423	No	

Finish:

White WT

Glass:

White WT

Material:

Steel

Certification:

Dry Location
N Location
CA Title 24

Additional:

Med Bi Pin T8 (Not Included)
Incandescent Watts: 509