



Lighting Your Life Since 1970

Product Specifications - 6204FTBK

Job Name:	Job Type:
Quantity:	Comments:



**6204FTBK**  
Outdoor Essentials 2-Light Outdoor Ceiling Mount

**Finish**  
Black

**Glass/Shade**  
Frosted

**Product Category**  
Outdoor Ceiling Mount

**Lamping**

Number of Bulbs	2
Light Type	Incandescent
Bulb Type	MB
Max Bulb Wattage	75
Max Fixture Wattage	150
Rated Life	±2,500 Hours
Rated Lumens	±1,600
Color Temp	±2,700 K
Bulb(s)	Not Included
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	No
Dimmable	Standard

**Measurements**

Width	9.5"
Height	5.0"
Length	N/A
Extension	N/A
Back Plate Width	N/A
Back Plate Height	N/A
HCO	N/A
Min Overall Height	N/A
Max Overall Height	N/A
Hanging Weight	4.0 lbs
Height Adjustable	N/A
Slope	N/A
Chain Length	N/A
Wire Length	N/A
Canopy Width	N/A
Canopy Height	N/A
Canopy Length	N/A

**Shipping**

Carton Weight	4.0 lbs
Carton Width	11"
Carton Height	7"
Carton Length	11"
Carton Cubic Feet	0.45
Master Pack	8
Master Pack Weight	37.0 lbs
Master Pack Width	22.1"
Master Pack Height	15.2"
Master Pack Length	22.1"
Master Cubic Feet	4.27
UPS Shippable	Yes

**Certification**

Safety Rating	Damp
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	No
Dark Sky	N/A

**Other**

UPC Code	783209620414
Shades Included	N/A
Crystals Included	N/A
Diffuser Included	N/A
Conversion Kit	N/A
Material	Steel

**Equivalents**

Incandescent Watts	N/A
Fluorescent Watts	N/A

Maxim Lighting International and all designs, logos and images © 2013 Maxim Lighting International. All Rights Reserved. Maxim Lighting International reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes.

Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.