



**Measurements:**

<u>Height</u>	<u>Width</u>		
20.50"	24.00"		
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
12.92 lb	5.00"	1.00"	5.00"

**Lamping:**

Incandescent MB  
 5.00 60W MB  
 300 total watt  
 Dimmable : Standard Dimmer  
 0 Rated Lumens  
 Color Temperature

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
17.26 lb	9.50"	22.50"	23.50"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209007659	Yes	

**Finish:**

Oil Rubbed Bronze OI

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Dry Location

**Additional:**

MB (Not Included)