


**Measurements:**

<u>Height</u>	<u>Width</u>	<u>Extension</u>
8.00"	13.25"	4.20"
<u>Hanging Weight</u>		
2.87 lb		



**Lamping:**

Incandescent MB Incandescent  
 2.00 60W MB Incandescent  
 120 total watt  
 Dimmable : Standard Dimmer

0 Rated Lumens  
 Color Temperature

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
4.01 lb	9.00"	6.00"	14.75"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209108448	Yes	

**Finish:**

Satin Nickel SN

**Glass:**

Frosted FT

**Material:**

Steel

**Certification:**

Damp Location

**Additional:**

MB Incandescent (Not Included)  
 Lighting Direction: BOTH