



Measurements:

Height

8.50"

BP Height

4.75"

Hanging Weight

7.04 lb

Width

28.50"

BP Width

8.00"

Lamping:

Incandescent MB Incandescent

0 Rated Lumens

4.00 60W MB Incandescent

Color Temperature

240 total watt

Dimmable : Standard Dimmer

Shipping:

Carton Weight

9.02 lb

Carton Width

6.50"

Carton Height

8.00"

Carton Length

31.00"

Master Pack Qty

1.0000

UPC

783209108653

UPS

Yes

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location

Additional:

MB Incandescent (Not Included)

Lighting Direction: BOTH