



*max overall height

Measurements:

Height

6.00"

Width

5.00"

Max OAH

50.50"

Hanging Weight

2.88 lb

Lamping:

Incandescent MB Incandescent

0 Rated Lumens

1.00 60W MB Incandescent

Color Temperature

60 total watt

Dimmable : Standard Dimmer

Shipping:

Carton Weight

Carton Width

Carton Height

Carton Length

3.32 lb

7.00"

6.25"

13.25"

Master Pack Qty

UPC

UPS

1.0000

783209108899

Yes

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Dry Location

Additional:

MB Incandescent (Not Included)

Slope: 120