



Measurements:

<u>Height</u>	<u>Width</u>
26.00"	12.75"
<u>Hanging Weight</u>	
6.35 lb	

Lamping:

Incandescent CA Incandescent E12	0 Rated Lumens
3.00 60W CA Incandescent E12	Color Temperature
180 total watt	
Dimmable : Standard Dimmer	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
8.95 lb	14.77"	16.14"	14.77"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209119048	Yes	

Finish:

Oil Rubbed Bronze OI

Glass:

Frosted FT

Material:

Steel

Certification:

Dry Location

Additional:

CA Incandescent E12 (Not Included)