



Image File Name:
F517-BN--
1378919677.jpg

Item #: F517-BN	UPC Code: 706411008641
Product Family Name: Concept™ I	Finish: Brushed Nickel
Category: Interior Fan	Category Type: Ceiling Fan
Certification E75795	
Patents U.S. Patent(s): D475,782; D476,408; D478,654; D478,980; 7,008,192	
Notes:	



MEASUREMENTS

Blade Finish:	Reversible Blades:	
	No	
Blade Material:	Slope:	
ABS Construction	Yes	
Blade Sweep:	No. of Blades:	Blade Pitch:
52	3	14 degrees
Downrod 1:	Downrod 2:	Hanging Weight:
3.5	6	25.40
Ceiling to Lowest Point: (Dim A)	Downrod 1 Outside Dia:	Downrod 2 Outside Dia:
15.00	.75	.75
Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
11.75	80	172x20mm

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	70		138		183
Amps:	0.32		0.49		0.51
Watts:	13.000		38.000		61.000
CFM:	2359.00		4929.00		6028.00
CFM/Watts:	181.46		129.71		98.82



FAN CONTROLS

Pull Chain Control: No	Works with Remote Control: Yes	Works with Wall Control: Yes
	Included Remote Control: RCS212	Included Wall Control:
	Compatible Remote Control[s]:	Compatible Wall Control[s]: WCS212

LAMPING

No. of Bulbs: 1	Light Type: Mini-Can Halogen
Max Bulb Wattage: 100	Socket: E11
Light Kit: Yes	Dimmable: Yes
Lamp Included: Yes	Ballast: Yes
	Rated Life Hours: Uplight
	Color Temp.: CR1
	Initial Lumens: Delivered Lumens:

GLASS

Description:	Material: Glass
Part No.: GF516A	Quantity: 1
Width:	Height:
	Length:



SHIPPING

Carton Width: 13.630	Carton Height: 12.130	Carton Length: 24.630
Carton Weight: 28.030	Carton Cubic Feet: 2.357	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 1



Title 17

UL Listed

Yes

Yes