



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Series G, LG-frame Molded Case Circuit Breaker

LGH3600FAG

UPC: 782116142781

**Dimensions:** 4.09 IN \* 5.48 IN \* 10.13 IN (L \* W \* H)

**Notes:** LG breaker is HACR rated

**Warranty:** Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 600A
- **Interrupt Rating:** 100 kAIC at 240V, 70 kAIC at 415V, 65 kAIC at 480V, 35 kAIC at 600V
- **Number Of Poles:** Three-pole
- **Frame Size:** LG-frame
- **Mounting Hardware:** Metric
- **Series:** Series G
- **Terminals:** Line and load
- **Trip Type:** Fixed thermal, adjustable magnetic

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [LG-frame Molded Case Circuit Breaker Drawing](#)
- [Installation Instructions for Series G L-Frame Circuit Breakers](#)
- [J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)
- [L-Frame 310+ Molded-case circuit breakers 100A-600A](#)
- [Molded case circuit breakers and power distribution blocks high short circuit current ratings](#)
- [Series G, L-frame Time Current Curves](#)



**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.