



S4189

20ALR12/FL32 FROST GBF
20 watt; Halogen; ALR12; GBF; Frosted; 1000 Average rated Hours; DC Bay base; 12 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output
- 12 volt



S4189

Item Number	UPC	Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S4189	045923041891	20	12	ALR12	DC Bay	BA15d	20ALR12/FL32 FROST GBF
ANSI Code	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
GBF	1-3/8"	1-1/2"	C-8	750	3000	Warm White	1000
Pack	Package Type	Beam Spread Deg	Lens	UV Block	Dimmable/Non-Dimmable	CEC Status	RoHS Compliant
200/20	Box	32	Y	Yes	Dimmable	Lawful for sale in California	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

