

Path Light 12V

15418AZT (Textured Architectural Bronze)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____



Dimensions

Height	21.50"
Width	7.00"

Ordering Information

Product ID	15418AZT
Finish	Textured Architectural Bronze

Specifications

Material	Aluminum
Glass Description	Clear Heat Resistant Glass

Electrical

Voltage	12V
Lead Wire Length	20.00"

Qualifications

Safety Rated	Wet
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Included
Number of Lights/LEDs	1
Max or Nominal Watt	20W
Socket Wire	105
Socket Type	Bi-Pin
Lamp Type	T3

Notes:

1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.

2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.