



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton custom safety switch

**DG322NGBLORED**

**UPC:**786685503578

### Dimensions:

- **Height:** 6.9 IN
- **Length:** 14.8 IN
- **Width:** 9.7 IN

**Weight:**9.68 LB

**Notes:**Includes lock-on provision and enclosure is painted red.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** General duty, single-throw safety switch
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 1
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Max Hp Rating:** 3-10, 7.5-15 hp at 240 V (1, 3 PH)
- **Maximum Voltage:** 240 Vac
- **Nema Rating:** NEMA Type 1
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire/four-wire
- **Product Category:** Safety switch
- **Switch Type:** General duty safety switch
- **Voltage Rating:** 240V

### Supporting documents:

- [Eaton Specification Sheet - DG322NGBLORED](#)

### Certifications:

- UL Listed



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.