


Elite BR Series

TCP Elite Series BR Lamps are great for illuminating large areas with smooth, attractive light.





TCP LED	Incandescent Replacement
17W BR40	120W BR40
12W BR30/40	85W BR30 & BR40
10W BR30	65W BR30
8W R20	50W R20

CRI 82

Perfect for most applications



Uniform flood light distribution



Item Number	ENERGY STAR® Item Description	Voltage	Lamp Watts	Lumens	Lumens Per Watt	Beam Angle	CCT	CRI	STK/MTD	Case Quantity	Dimmable Elite LED BR Lamps
12W ELITE DIMMABLE BR30 (REPLACES 85W)											
LED12BR30D24K	12W Smooth BR30 - 2400K	120	12	850	70.8	110	2400K	82	STK	12	
LED12BR30D27K	★ 12W Smooth BR30 - 2700K	120	12	850	70.8	110	2700K	82	STK	12	
LED12BR30D30K	12W Smooth BR30 - 3000K	120	12	875	72.9	110	3000K	82	STK	12	
LED12BR30D41K	12W Smooth BR30 - 4100K	120	12	900	75.0	110	4100K	82	STK	12	
LED12BR30D50K	12W Smooth BR30 - 5000K	120	12	900	75.0	110	5000K	82	STK	12	
10W ELITE DIMMABLE BR30 (REPLACES 65W)											
LED10BR30D24K	10W Smooth BR30 - 2400K	120	10	650	65.0	110	2400K	82	STK	12	
LED10BR30D27K	★ 10W Smooth BR30 - 2700K	120	10	650	65.0	110	2700K	82	STK	12	
LED10BR30D30K	10W Smooth BR30 - 3000K	120	10	675	67.5	110	3000K	82	STK	12	
LED10BR30D41K	10W Smooth BR30 - 4100K	120	10	700	70.0	110	4100K	82	STK	12	
LED10BR30D50K	10W Smooth BR30 - 5000K	120	10	700	70.0	110	5000K	82	STK	12	

LED Lamps

★ ENERGY STAR® Rated (at time of print)



*Based on 12 Hours per day