



A3647

25G25
25 watt G25 Incandescent; Clear; 3000 average rated hours;
180 lumens; Medium base; 130 volts

Features

- Decorative incandescent
- Long Life
- Brass Base
- 130 volt



A3647

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
A3647	045923036477	25	G25	Medium	E26	25G25	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Clear	4-3/8"	3.13"	CC-9	180	3000	72/6	Box

Dimmable/Non-Dimmable	CEC Status	RoHS Compliant
Dimmable	Lawful for sale in California	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

