



*Hoffman*

## Lay-In NEMA Type 12 Wireway Straight Section

Catalog Number: F44L120  
US List Price (USD): \$367.60

### Bulletin Number:

- F10

### Material:

- Steel



### Model Code:

- 18300

### Ship Wt. Std. Pkg. (lbs):

- 51.0

### Interchangeable:

- False

### IP Rating:

- IP54

## Description

---

Available in lengths from 6.00 in. (152 mm) to 120.00 in. (3048 mm).

### Description:

Available in lengths from 6.00 in. (152 mm) to 120.00 in. (3048 mm).

### Notes:

- Each sealing plate also includes one gasket and one set of screws to join sections.
- Certified by Canadian Standards Association.

## Technical Data

---

### Lay-In NEMA Type 12 Wireway Straight Section

<b>Catalog Number</b>	<a href="#">F44L120</a>
<b>A in.</b>	4
<b>B in.</b>	4
<b>C in.</b>	120
<b>D in.</b>	5.38
<b>E in.</b>	5.38
<b>Sealing Plates Type</b>	Flat
<b>Sealing Plates Qty.</b>	1

## Certifications

---



UL Certification

## Documents

---



3D STEP CAD



2D DXF CAD



Spec Sheet



DOC



Dimension Drawing

No accessories available.