



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety : Switch

DH363URK

UPC: 782113206479

Dimensions: 22.5 IN * 12.5 IN * 8.5 IN (L * W * H)

Notes: Suitable for service entrance use with a neutral or ground lug kit installed

Warranty: Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Configuration:** Non-fusible
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Non-Fusible
- **Voltage Rating:** 600V
- **Max Hp Rating:** 20 at 240 Vac TD 1 Ph, 40 at 480 Vac TD 1 Ph, 50 at 600 Vac TD 1 Ph, 40 at 240 Vac TD 3 Ph, 75 at 480 Vac TD 3 Ph, 100 at 600 Vac TD 3 Ph, 20 at 250 Vdc

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Drawing Dataset](#)
- [Eaton Specification Sheet - DH363URK](#)

Certifications: No Data

Product compliance: No Data

