



**OL11200DWZ: 5" LED Outdoor Sconce**



**Dimensions:**

**Width:** 5"      **Extends:** 3 3/8"  
**Height:** 5"      **Wire:** 8"  
**Mounting Proc.:** Cap Nuts  
**Connection:** Mounted To Box  
**Bulb Type:** Array  
**Bulb Base:** Integrated  
**Volts:** 120  
**Watts:** 8  
**Watts Consumed:** 8  
**Watts Rated:** 8  
**Hours Rated:** 30000  
**Lumens:** 600  
**Bulb Temp:** 2700 °K  
**CRI:** 90

**Features:**

- Meets American with Disabilities Act standard extension requirements
- This advanced LED technology is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

**Material List:**

1 Body - Steel - Dark Weathered Zinc

**Safety Listing:**

Safety Listed for Wet Locations

**Instruction Sheets:**

Trilingual (English, Spanish, and French)  
 (OL11200\_OL11201\_OL11202\_OL11203\_)

**Collection:** Legend

**UPC #:** 014817541199

**Finish:** Dark Weathered Zinc (DWZ)

**Shade / Glass / Diffuser Details:**

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	White	1									

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	OL11200DWZ	1	014817541199	12.75	8.25	9.78	0.595	2.55	150	Yes
NJ Pallet		126		48	40	77	85.556	327.6		No
NV Pallet		96		48	40	78	86.667	244.8		No