

Flush Round Single or Multi-Service Non-Metallic Floor Boxes, for Use In Concrete Floors

Min. Depth of Pour	3.00" (76.2)
Cubic Inch (cm³) Capacity	100 cu. in. (1638.7 cm ³) prior to cutting level to floor (19.5 cu. in. (313.2 cm ³) per inch of depth).
Dimensions – A	6.00" (152.4)
Dimensions – B	7.08" (179.8)
Dimensions – C	6.69" (169.9)
Dimensions – D	5.38" (136.5)
Hubs	(2) 1" and (2) 3/4" Conduit Hubs
Concrete Cover Included	✓
Closure/Reducer Plugs	(2) 1" plugs close off 1" hubs or reduce 1" to 3/4" (2) 3/4" plugs close off 3/4" hubs or reduce 3/4" to 1/2"

Note: UL File Number E92074. CSA File Number LR18416.

Description	Catalog Number
Adapter Required for all applications.	PFBA1A
Low Voltage Divider Required for use with catalog number PFB1 when used in multi-service applications. Accepts Hubbell standard duplex receptacles or 15A Twist-Lock® duplex receptacles (HBL4700 series).	PFBT1A
"Y" Adapter 3/4 in. "Y" adapter to feed parallel runs of 3/4 in. conduit.	PFBYA1
Pre-pour PVC stand increases PFB1 box height 2.5 in. to 4.0 in. within the concrete pour.	PFBSTAND

Flush Round Covers and Flanges

Multi-Service Cover and Flange Assemblies
Includes floor box cover with duplex flaps, (2) 1/2 in. dia. low voltage feed through holes and matching carpet flange. 6.25 in. Diameter

SF39253A	PFBCBRA	PFBCBLA	PFBCGYA	PFBCIA
Brass	Brown Non-Metallic	Black Non-Metallic	Gray Non-Metallic	Ivory Non-Metallic

Metal Carpet Flange

Use with single service covers for carpet applications. 6.25 in. Diameter

S3082	SA3082
Brass	Brushed Aluminum

Adapter Ring

Use with single service covers for tile applications.

S5016	SA5016
Brass	Aluminum

Multi-Service Replacement Covers

Material	Metallic	Color	Non-metallic
Solid Brass	BRS2RCA	Black Brown Gray Ivory	PFBCBCLA PFBCBBRA PFBCBGYA PFBCBIA

Single Service Covers

Brass
Aluminum
3.88 in. Dia.

S3925	S3725	S2525	S2725	S2925	S3525	S3325
SA3925	SA3725	SA2525	SA2725	SA2925	—	—
Duplex Flap	Duplex Screw	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	2 3/8" Single Receptacle	2 1/8" Single Receptacle (Terrazzo Floor)

One Piece Brass Cover and Carpet Flange

Brass
Aluminum
6.25 in. Dia.

SF3925	SF2525	SF2725	SF2925
SFA3925	—	—	—
Duplex Flap	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle

Note: Adapter ring S5016 is required for mounting SF series covers onto PFBA1A.

Dimensions in Inches (mm)

Furniture Feed Plate

Unpainted plate with 1 in. threaded opening.

PFBP1
Steel