

Duplex Connectors

2 Screw - Clamp Type - For BX-Flex, NM & MC Cable - Zinc

Features

- Duplex 2 screw clamp type
- UL listed locknut
- Male hub NPT
- Tri-combo screw head




Applications

- Indoor dry location use only
- Strap-type fitting used to connect flexible metal conduit or armored cable to box or enclosure



Standard Material

- Zinc die cast
- Zinc plated steel strap



Catalog Number	UPC	BX Flex Size	KO	Unit Carton	Ship Case	Weight/Case	Inches	
							A	B (Min. - Max.)
360	13500	3/8"	1/2"	25	250	32	1.68	.24 - .63

Cable type	Cable size	Cable Diameter
Armored Cable, Steel	14/2 - 10/3	.48-.58
Armored Cable, Aluminum	14/2 - 10/3	.46-.50
MCI-Aluminum	14/2 - 10/3	.488-.810
MCI-Steel	14/2 - 10/3	.47-.60
MCI-A, Aluminum	14/2 - 10/3	.370-.495
HCF, MCI A Aluminum	12/2 - 10/2	.418-.495