LED-8090M 120W LED for HID Retrofit for Shoebox/Wallpack

LED HID RETROFIT

Models

LED-8090MXT3, 120-277VAC, ULus, 4000K or 5000K CCT, E39 LED-8090MXC3,120-347VAC, cUL, 4000K or 5000K CCT, E39




Features

- > 120W LED Replaces 400W MH or HPS HID Lamps
- > Rotatable base enables user to accurately direct output to target
- > Designed for Horizontal installations
- > UL approved for damp environments and enclosed fixtures
- > Advanced active cooling: Active cooling and dynamic temperature control
- > 50,000 hour rated LED life (supported by LM80 and ISTMT reports (see website)
- > 5 Year Limited Warranty see website for details

> 5 Year Limited Warranty - see website for details			
Technical S	pecificatior	IS	
Models US/CAN	LED-8090M4T3/ LED-8090M4C3	() LED-8090M5T3 / LED-8090M5C3	
ССТ	4000K	5000K	
Power Consumption	120	watts	
Replaces	400 MH/HPS		
Mounting	E39		
Voltage	120-277VAC (USA) 120-347VAC (CANADA)		
LED Type	CREE XTE		
Beam Angle	Type III		
Dimmable	No		
Operating Temp	-40°F - +122°F		
Rated R70 Life	Up to 50,000 Hrs.		
Warranty	5 Year Limited*		
LM79 Specifications	Yes	Yes	
Power (W)	120	120	
ССТ	4144	5000	
Light Output	9591	10434	
Efficacy	81.49	92.28	
THD @ 277V	18.86%	19.23%	
PF @ 277V	0.918	0.918	
CRI:	84.6	69.5	
R9	18	0	
Duv	0.0008	0.0063	
Packaging	9 / Master Carton		
Unit	6.6"x 6.6"x 12.9" 2.9lbs.		
Master	20.7"x 18.5" x 13.8" 25.5 lbs.		



Lux Distance Curve



Г		\wedge	
	3888.5lux		2.8m
1.0m		VI _D	
2.0m	972.1lux	·ion or	5.7m
2.011		Chart for Position only	
3.0m	432.1lux	art for	8.5m
	243.0lux	Cho	11.4m
4.0m			
5.0	155.5lux		14.2m
5.0m			

Beam angle of C90plane109.74

LED Power Consumpti on (Watts)	Power	HID Ballast Power Consumpti on (Watts)	Total Savings (Watts)	Annual Energy Savings (14 hrs/day)	Lifetime Energy Savings (over 50,000 hrs)
120	400	80	360	\$202	\$1,980.00

Mounting Orientation		Minimum Fixture Size		
Base Up	Base Down	Horiz	Requirements (inches)	
			Length	13.26
<u> </u>			Width	6.33
			Height	6.33
			Cu. Inches	531.3
Approved	Approved	Approved	Cu. Inches	551.5

