

Catalog Number: G 978
Product ID: 7TAA004780R0055
UPC Number: 78599178220
Status: Active

Channel Joiner, Material Steel, Length 7-1/2 Inches, Depth 1-1/2 Inch, For use with G 975, G975 M, B 900 and B900 M, Installed by Tightening Nuts on 1/4 Inch Stud

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	31162502 Angle brackets
IGCC	3010 Angle brackets
Brand Name	Kindorf
Type	Surface Raceway & Lighting Support Systems
Application	To splice lengths of raceway channel. Installed by tightening nuts on 1/4 in. studs which are permanently attached to a smooth inner plate.
Standard	UL e55274
Material	Steel
Length	7-1/2 Inches
Depth	1-1/4 Inches
Finish	Galv-Krom/Standard
Number Of Holes	4
Thickness	14 Gauge

European Specifications (ETIM)

ETIM	EC000483 Coupler for support/profile rail
Suitable for	U-profile
Model	Exterior coupler
With screw accessories	N
Material	Steel
Surface protection	Other

Packaging

Outer Quantity	20
Outer Dimensions (inches)	12.25x8.5x4.75
Weight Uom	112.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com