

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Circline fluorescent

P7251-09EBWB

Modular Fluorescent

Oval fluorescent with acrylic diffuser and decorative metal encloser. T-9 fluorescent lamps included. Energy Star.

Category: Modular Fluorescent

Finish: Brushed Nickel (plated)

Construction: Steel construction

Glass: White acrylic diffuser

Width: 18"

Length: 32-1/2"

Height: 4-3/8"

Glass: 30-11/16"

Height: 3-15/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
<p>Ceiling mounted</p> <p>Mounting strap for outlet box included</p> <p>Ceiling pan covers a standard 4" hexagonal recessed outlet box</p>	<p>Pre-wired</p> <p>120V NPF electronic</p> <p>120V</p>	<p>Quantity: 2</p> <p>32W T9 Circline (included)</p> <p>4-pin circline lamp holders</p>	<p>UL-CUL Damp location listed</p> <p>1 year warranty</p> <p>Companion fixtures are available</p> 