



Hoffman

Medium, Type 1

Catalog Number: A20N16ALP
US List Price (USD): \$207.10

Bulletin Number:

- A1M

Material:

- Steel



Model Code:

- 85960

Ship Wt. Std. Pkg. (lbs):

- 21.0

Interchangeable:

- False

IP Rating:

- IP30

Industry Standards:

UL 50, 50E Listed; Type 1; File No. E27567 cUL Listed per CSA C22.2 No 40; Type 1; File No. E27567 NEMA/EEMAC Type 1 CSA, File 42184: Type 1 IEC 60529, IP30

Description

These enclosures have a size range of 16 x 12 x 6-in. to 36 x 30 x 12-in. and meet basic functionality requirements for applications that do not require oil- or dust-tight enclosures.

Applications:

These enclosures have a size range of 16 x 12 x 6-in. to 36 x 30 x 12-in. and meet basic functionality requirements for applications that do not require oil- or dust-tight enclosures.

Features:

- Doors have butt hinges
- Collar studs provided for mounting optional panel
- Slotted flush latches; optional latches available
- Mounting holes on back of enclosure

Specifications:

14 or 12 gauge steel

Finish:

ANSI 61 gray polyester powder paint finish inside and out over pretreated surfaces. Optional solid panels are white and optional perforated panels are gray.

Accessories:

- T-Handle Latch and Keyed Cylinder Lock Kits
- Electric Heater
- Electrical Interlocks
- Grounding Device
- Panels for Medium Type 1 Enclosures
- Rack Mounting Angles - U Style (Type RA)
- T-Handle Latch and Keyed Cylinder Lock Kits
- Touch-Up Paint
- Steel and Stainless Steel Window Kits

Notes:

- Purchase panels separately.
- The following Perforated Panels are flanged on four sides: A24N24MPP, A30N20MPP, A30N24MPP, A30N30MPP, A36N24MPP and A36N30MPP.

Technical Data

Medium, Type 1

Catalog Number	A20N16ALP
A in.	20
B in.	16
C in.	6.62
K in.	1.50
F in.	6.00
G in.	17.88
H in.	11.00
Panel Size D x E in.	17.00 x 14.50
J in.	2.50
Q in.	1.06
P in.	0.31
Panel	A20N16MP
Perforated Panel	A20N16MPP
Panel Gauge	14

Certifications



EU Certification



UL Certification

Documents



Instruction Manual



Instruction Manual



Spec Sheet



2D DXF CAD



3D STEP CAD



DOC



Dimension Drawing

No accessories available.