


Grounding - Steel

Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 2.18
Dimension B in Inches: 3.03
Dimension C in Inches: 0.73
Dimension D in Inches: 2.27
Dimension E in Inches: 3.37

Application

Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated Grounding bushing is required. Grounding lug, aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed. Patented

Product Information

Material: Steel
Finish: Zinc Plated, Grounding Lug, Tin Electro-Plate

Certifications & Codes:

Federal Specification Number: A-A-50553
NEMA Standard: FB-1
UL File Number: E20412
UL Standard: UL-514B
UNSPSC: 39121312

Catalog ID: SGBS-387CL

UPC Number: 78174723870

Description: Split Bushing, Insulated, Grounding, Zinc Plated Steel, Size 2-1/2 Inch

Application: Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated Grounding bushing is required. Grounding lug, aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed. Patented

Trade Size: 2-1/2"

Std Pkg Qty: 25

Unit Qty: -