



Representative

**Catalog Number:** 54811  
**Product ID:** 7TAH007510R0010  
**UPC Number:** 78621054811  
**EAN Number:** 05414363110781  
**Status:** Active

Copper Two-Way Splice, Long Barrel, Max 354kV, Wire Size 3/0 AWG, Length 2.25 Inches, Diameter 0.65 Inch, Tin Plated, Die Code Orange, Die Color Code Orange

- Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Color-Keyed
Type	Splice Connector
Special Features	Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.
Standard	UL E9809, CSA 4503
Material	Copper
Finish	Tin-Plated
Color	Orange
Voltage Rating	600V

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	100
Outer Dimensions (inches)	12.6x6.4x4
Weight Uom	9.06 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00674-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)