



GE  
Lighting

39405 - null

LED7DMRX16827/35

Product Photo



#### GENERAL CHARACTERISTICS

Primary Application	Track & Recessed
Product Technology	LED
Rated Life (Hours)	25000 h
Base	GU5.3

#### PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	35 deg
Center Beam Candle Pwr Candela	1000 cd
Nominal Initial Lumen per Watt	57.1
Rated Beam Spread	35 deg
Initial Lumens-nominal	400 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

#### PRODUCT INFORMATION

Product Code	39405
Description	LED7DMRX16827/35
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168394055
Standard Package GTIN	00043168394055
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168394055
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168394055
Standard Package GTIN	10043168394052
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168394055

#### DIMENSIONS

Bulb Max Overall Length-MOL	2.2 in
-----------------------------	--------

#### ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V